

MONO

A020PJ1050L51-10 RAL7035

EAN 4031582359879



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ● ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Mono
Tip kućišta	Okretanje Tocak
Standard	EN12528 - točkovi za nameštaj
Nosivost na 3 km/h	30 kg
Statički Nosivost	60 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	72 mm
Ukupna težina	0,54 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	klizni lezaj sa caura cevi
stitnici omotaca	Bez stražara
Prečnik	50 mm
Širina omotac	18 mm
Teškoća gazećeg omotac (A)	85 Šora A

KUCISTE

Materijal	polipropilen
oblik viljuska	Zatvoreno
okretni lezaj	stablo , okretanje
ofset	25 mm
okretni radijus	52,2 mm
Otpor okretanju	104,4 mm

PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

MONO

A020PJI050L51-10 RAL7035

EAN 4031582359879



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

