

PURETECH

JYX 150X32-Ø8,3 CLIP

EAN 4031582319972
Order number 00024890



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Zinc die-cast
	soft
Tread material	Solid rubber, black, electric-conductive
Bearing	Precision ball bearing, sealed
Wheel color	Metallic
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Axle hole diameter	0.33 in
Hub length	1.4 in
Body width	1.26 in
Hardness of tread (A)	75 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	330.69 lb
Electric conductive	✓
Load capacity Static	661.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.97 lb

PRODUCT INFORMATION

PURETECH

JYX 150X32-Ø8,3 CLIP

EAN 4031582319972
Order number 00024890



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

