

PURETECH

2895ZIP125P72 GAUCHE TFR

EAN 4031582386554



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	161 mm
Overall weight	0.916 kg

WHEEL

Body material	Flanged wheel
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Special Function
Offset	43 mm
Swivel interference	211 mm

FITTING

Fitting type	Vertical flange
--------------	-----------------