

NOVATECH

FTP 250X80-Ø25 HL92

EAN 4031582319415

Broj porudžbine 00800997



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
štitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	80 mm
dimenzija rupa osovina	25 mm
dužina glavcine	92 mm
Širina tela	80 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja ● ● ● ● ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	2160 kg
Nosivost na 6 km/h	1800 kg
Statički Nosivost	3600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	9,22 kg

NOVATECH

FTP 250X80-Ø25 HL92

EAN 4031582319415

Broj porudžbine 00800997



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

