

# DURATECH

TOP 085X80-Ø20 HL80

EAN 4031582331202

Broj porudžbine 00832614



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	85 mm
Širina omotac	80 mm
dimenzija rupa osovina	20 mm
dužina glavcine	80 mm
Širina tela	80 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	750 kg
Nosivost na 6 km/h	600 kg
Statički Nosivost	1500 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,558 kg

# DURATECH

TOP 085X80-Ø20 HL80

EAN 4031582331202  
Broj porudžbine 00832614



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

