PRODUCT INFORMATION

BASETECH

POO100X36-Ø12 HL44,4 BLANCA

EAN 4031582442618

BETTER MOBILITY. BETTER LIFE.

Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	36 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (D)	65 Shore D

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.105 kg

© Copyright 2026 TENTE International GmbH

BASETECH

POO100X36-Ø12 HL44,4 BLANCA

EAN 4031582442618

BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



© Copyright 2026 TENTE International GmbH