

ELASTECH HEAT

IDC 100x35-Ø8,3 HL45 tread-1023 INOX

EAN 4031582348620



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech heat
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	80 kg
Električni provod	no
nerdjajuci	yes
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-30 °C
Opseg temperature (maksimalni)	250 °C
Ukupna težina	0.57 kg

TOCAK

Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Vlažnost, otpornost na visoke temperature
Nošenje	precizini kuglicni lezaj, nerdjajuci
Boja Tocak	Metalni
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
dimenzija rupa osovina	8.3 mm
duzina glavine	45 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	75 Šor A

ELASTECH HEAT

IDC 100x35-Ø8,3 HL45 tread-1023 INOX

EAN 4031582348620



BETTER MOBILITY. BETTER LIFE.

Product Drawings

