

ELASTECH HEAT

IDG100X35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Elastech heat
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Electric conductive	✓
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall weight	0.354 kg

WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Damping, heat resistant
Bearing	Dry bearing bush
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (A)	75 Shore A

ELASTECH HEAT

IDG100X35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

