

# DURATECH HEAT

IOG 100X35-Ø8,4 CLIP

EAN 4031582347234  
Order number 00034267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle hole diameter	8.4 mm
Hub length	45 mm
Body width	35 mm
Hardness of tread (D)	95 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Stainless	✓
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.341 kg

# DURATECH HEAT

IOG 100X35-Ø8,4 CLIP

EAN 4031582347234  
Order number 00034267



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

