

# NOVATECH

RK.ETP100X40-Ø47X14

EAN 4031582369588  
Order number 00839713



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Undefined           |
| Tread material        | Polypropylene, soft |
| Diameter              | 3.94 in             |
| Tread width           | 1.57 in             |
| Hardness of tread (A) | 92 Shore A          |
| Ball bearing diameter | 1.85 in             |
| Ball bearing width    | 0.55 in             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |            |
|-----------------------------|------------|
| Product name                | Novatech   |
| Housing type                | Wheel      |
| Load capacity at 1.8 mph    | 1102.31 lb |
| Load capacity Static        | 2204.62 lb |
| Temperature range (Minimum) | -4 °F      |
| Temperature range (Maximum) | 140 °F     |

## TECHNICAL DRAWINGS

