

DURATECH HEAT

WOG 075x25 HL31,8 black

EAN 4031582382891



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Wheel Color	Black
Diameter	75 mm
Tread width	25 mm
Axle Hole Diameter	8 mm
Hub Length	31.8 mm
Body width	25 mm
Hardness of tread (D)	80 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	100 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	134 °C
Overall weight	0.08 kg

DURATECH HEAT

WOG 075x25 HL31,8 black

EAN 4031582382891

Order number 00039564
Product Drawings



BETTER MOBILITY. BETTER LIFE.

