

PRODUCT INFORMATION

NOVATECH

ETP085x90-Ø17 HL90

EAN 4031582369465



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	1763.7 lb
Electric conductive	no
Stainless	no
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.35 in
Tread width	3.54 in
Axle hole diameter	0.67 in
Hub length	3.54 in
Hardness of tread (A)	92 Shore A
Bearing type	6303

