

# STORA

2370PJJ100P30-11

EAN 4031582300321



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.08 in
Overall weight	1.19 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Offset	1.38 in
Swivel radius	3.35 in
Swivel interference	6.69 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

# STORA

2370PJJ100P30-11

EAN 4031582300321



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

