

# AGILA

2477UAP100P30-13

EAN 4031582365238  
Order number 00031222



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 100 kg                        |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -25 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall height              | 135 mm                        |
| Overall width               | 60 mm                         |
| Overall weight              | 0.803 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver grey (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 100 mm                 |
| Tread width           | 32 mm                  |
| Body width            | 32 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Colour              | Blue passivated     |
| Offset              | 43.5 mm             |
| Swivel radius       | 131 mm              |
| Swivel interference | 262 mm              |
| Dome diameter       | 60 mm               |

## FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 13 mm                                                      |
| Hint               | Castors can be mounted with standard screws of any length. |

## PRODUCT INFORMATION

# AGILA

2477UAP100P30-13

EAN 4031582365238  
Order number 00031222



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

