

LINEA

5940UAP150P52 RAL7001

EAN 4031582411522



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●●

Buka u pokretu ●●●●○

Ishrana ●●●●○

otpornost na rdju ●●●●○

OSNOVNI ATRIBUTI

Naziv proizvoda	Linea
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	110 kg
Statički Nosivost	220 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	170 mm
Ukupna širina	89 mm
Ukupna težina	1,1 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	22 mm
Teškoća gazećeg omotac (A)	92 Šor A

KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	precizini kuglicni lezaj
Boja	Srebrna siva (RAL7001)
ofset	52 mm
okretni radijus	133 mm
Otpor okretanju	218 mm
Prečnik kupole	56 mm

PRILAGOĐAVANJE

Tip uklapanja	Pravougaona ploča, razmak otvor za vijak
Dužina ploče	90 mm
Širina ploče	75 mm
Dužina otvora ploče (Minimalno)	72 mm
Dužina otvora ploče (maksimalna)	76 mm
Širina otvora ploče (Minimalno)	44,5 mm
Širina otvora ploče (maksimalna)	52 mm
Prečnik otvora ploče	11 mm

Deutscher
dizajner
ClubInterzum
nagradaIF nagrada za
Dizajn

LINEA

5940UAP150P52 RAL7001

EAN 4031582411522



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

