

AGILA

2470PIO150P30-11

EAN 4031582361162



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Agila
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	185 mm
Ukupna težina	0,764 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	klizni lezaj
štitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

KUCISTE

Materijal	Čelični list, srednji
oblik viljuskas	siroko
okretni lezaj	Dve lopte
ofset	45 mm
okretni radijus	120 mm
Otpor okretanju	240 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm
Savet	Kastori se mogu montirati standardnim vijcima bilo koje dužine.

AGILA

2470PIO150P30-11

EAN 4031582361162



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

