

# SUPRATECH

PJR100x32-Ø12 HL34,9

EAN 4031582320510



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Supratech                 |
| Type                        | Wheel                     |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall weight              | 0.16 kg                   |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread Material Mix    | Thermoplastic rubber |
| Bearing               | Roller bearing       |
| Threadguards          | Without threadguard  |
| Diameter              | 100 mm               |
| Tread width           | 32 mm                |
| Axle Hole Diameter    | 12 mm                |
| Hub Length            | 34.9 mm              |
| Hardness of tread (A) | 87 Shore A           |

# SUPRATECH

PJR100x32-Ø12 HL34,9

EAN 4031582320510

Order number 00030823  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

