PRODUCT INFORMATION

# ALPHA

3471PVR200P63

EAN 4031582383799

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●○○○ |
| Corrosion resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Alpha |
| Type | Swivel caster with directional lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 451.95 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 903.89 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 9.45 in |
| Overall weight | 6.15 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 2.17 in |
| Swivel interference | 12.2 in |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Solid rubber, black |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 7.87 in |
| Tread width | 1.97 in |
| Hardness of tread (A) | 85 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 5.39 in |
| Plate width | 4.13 in |
| Plate hole length (Maximum) | 4.13 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 3.15 in |
| Plate hole diameter | 0.43 in |

© Copyright 2026 TENTE International GmbH


# ALPHA


3471PVR200P63


EAN 4031582383799


BETTER MOBILITY. BETTER LIFE.

## Product Drawings






© Copyright 2026 TENTE International GmbH