

PURETECH

PVO250X50-Ø20 HL58

EAN 4031582442380



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll performance	● ● ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	2.06 kg

PURETECH

PVO250X50-Ø20 HL58

EAN 4031582442380



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

