

BASETECH

POL5x2-Ø1/2

EAN 4031582387612



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Basetech
Type	Wheel
Load capacity at 3 km/h	294 kg
Electric Conductive	No
Stainless	No
Load capacity Static	588 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing with hub tube
Diameter	127 mm
Tread width	50.8 mm
Axle Hole Diameter	12.7 mm
Hub Length	63.5 mm

BASETECH

POL5x2-Ø1/2

EAN 4031582387612



BETTER MOBILITY. BETTER LIFE.

Product Drawings

