

NOVATECH

ITP 150x50-Ø20 HL60

EAN 4031582319897



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ● ○
Buka u pokretu	● ● ● ● ○ ○
Ishrana	● ● ● ● ● ○
otpornost na rdju	● ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	650 kg
Nosivost na 6 km/h	520 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1300 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1.18 kg




NOVATECH

ITP 150x50-020 HL60

EAN 4031582319997

Broj porudžbine 00829121



BETTER MOBILITY. BETTER LIFE.