PRODUCT INFORMATION

MAXTECH

PAO100x25-Ø6x27 + ASBUS

EAN 4031582381245

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Diameter	100 mm
Tread width	25 mm
Axle Hole Diameter	6 mm
Hub Length	27 mm

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.11 kg

© Copyright 2026 TENTE International GmbH