PRODUCT INFORMATION

ANIKA

5923UAI065L51-10 Dom18

EAN 4031582437782

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Anika
Type	Swivel castor with intermittend brake
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	67 mm
Overall width	39.5 mm
Overall weight	0.08 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Offset	20 mm
Swivel radius	55.4 mm
Swivel interference	110 mm
Dome diameter	18 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	11 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

interzum Interzum Award

© Copyright 2026 TENTE International GmbH


ANIKA

5923UAI065L51-10 Dom18

EAN 4031582437782

BETTER MOBILITY. BETTER LIFE.

Product Drawings



Interzum Award

© Copyright 2026 TENTE International GmbH