

# ZETA

4680FTP125P63 TFR

EAN 4031582390506



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	660 kg
Load capacity at 6 km/h	550 kg
Load capacity Static	1320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	164 mm
Overall weight	4.6 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	125 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel radius	117.5 mm
Swivel interference	235 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ZETA

4680FTP125P63 TFR

EAN 4031582390506



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

