

NOVATECH

ETY080X20-Ø20 HL14

EAN 4031582419047



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Diameter	80 mm
Tread width	20 mm
Axle hole diameter	20 mm
Hub length	14 mm
Hardness of tread (A)	92 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 3 km/h	140 kg
Load capacity Static	280 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.3 kg

TECHNICAL DRAWINGS

