

MAXTECH

PNP 175x30-Ø8 HL44

EAN 4031582320602



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	165.35 lb
Electric conductive	no
Stainless	no
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.66 lb

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel color	Black
Threadguards	With threadguard
Diameter	6.89 in
Tread width	1.18 in
Axle hole diameter	0.31 in
Hub length	1.73 in
Body width	1.18 in
Hardness of tread (A)	70 Shore A

MAXTECH

PNP 175x30-Ø8 HL44

EAN 4031582320602

Order number 00005566
Product Drawings



BETTER MOBILITY. BETTER LIFE.

