

# COMPACTA

1430PVH065P60-75X60

EAN 3700001796755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	85 mm
Overall weight	0.143 kg

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	65 mm
Tread width	25 mm
Hardness of tread (A)	85 Shore A

## HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Offset	25 mm
Swivel radius	57.5 mm
Swivel interference	115 mm

## FITTING

Fitting type	Rectangular plate
Plate length	75 mm
Plate width	60 mm
Plate hole length (Maximum)	55 mm
Plate hole width (Maximum)	40 mm
Plate hole diameter	7 mm

PRODUCT INFORMATION

# COMPACTA

1430PVH065P60-75X60

EAN 3700001796755



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

