

# ALPHA

3478DYJ125P62

EAN 4031582377118  
Order number 00035452



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Housing type                | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 220.46 lb                     |
| Electric conductive         | ✓                             |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 6.1 in                        |
| Overall weight              | 2.11 lb                       |

## WHEEL

|                       |  |
|-----------------------|--|
| Body material         | Sheet Steel                              |
| Tread material        | Solid rubber, black, electric-conductive |
| Bearing               | Roller bearing                           |
| Axle                  | Screwed with nut                         |
| Threadguards          | With threadguard                         |
| Diameter              | 4.92 in                                  |
| Tread width           | 1.46 in                                  |
| Hardness of tread (A) | 85 Shore A                               |

## HOUSING

|            |                    |
|------------|--------------------|
| Material   | Steel sheet, heavy |
| Fork shape | Broad              |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 4.06 in           |
| Plate width                 | 3.35 in           |
| Plate hole length (Minimum) | 3.03 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Maximum)  | 2.36 in           |
| Plate hole diameter         | 0.35 in           |

# ALPHA

3478DYJ125P62

EAN 4031582377118  
Order number 00035452



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

