

ZETA

4681TOO125P63

EAN 4031582308013
Order number 00830074



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Housing type	Swivel castor with directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1543.23 lb
Load capacity at 3.7 mph	1234.59 lb
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	6.46 in
Overall weight	5.71 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	2.17 in
Swivel interference	9.06 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ZETA

4681TOO125P63

EAN 4031582308013
Order number 00830074



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

