

PRODUCT INFORMATION

FOOTMASTER

FOOT MASTER GDR- 60-S-NYN

EAN 4031582413304



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	250 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	82.5 mm
Overall width	70 mm
Overall weight	0.7 kg

HOUSING

Housing Color	White
Offset	38 mm
Swivel radius	63 mm
Swivel interference	126 mm
Dome diameter	70 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	50 mm
Tread width	25 mm
Body width	25 mm

FOOTMASTER

FOOT MASTER GDR- 60-S-NYN

EAN 4031582413304

Order number 00062081

Product Drawings



BETTER MOBILITY. BETTER LIFE.

