PRODUCT INFORMATION

PURETECH

DIK 075x25-Ø6,1

EAN 4031582070149



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread Material Mix	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel Color	Blue passivated
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Axle Hole Diameter	6 mm
Hub Length	28 mm
Body width	25 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	55 kg
Electric Conductive	No
Stainless	No
Load capacity Static	110 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.22 kg

© Copyright 2026 TENTE International GmbH


PURETECH

DIK 075x25-Ø6,1

EAN 4031582070149

Order number 00004955

Product Drawings



© Copyright 2026 TENTE International GmbH