PRODUCT INFORMATION

MAXTECH

UAP 200x50-Ø25 HL60 natural/3004

EAN 4031582323061



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	96 Shore A
Hardness of tread (D)	48 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1102.31 lb
Load capacity at 3.7 mph	881.85 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	2.58 lb

© Copyright 2026 TENTE International GmbH


MAXTECH

UAP 200x50-Ø25 HL60 natural/3004

EAN 4031582323061

Order number 00034873

Product Drawings



© Copyright 2026 TENTE International GmbH