

# LINEA CLINIC

5946UAC125R36-32S30OH150 4XM6

EAN 4031582360028



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                        |
|-----------------------------|----------------------------------------|
| Product name                | Linea clinic                           |
| Housing type                | Swivel castor with central, total lock |
| Standard                    | similar EN12531- Hospital Bed Castors  |
| Load capacity at 3 km/h     | 150 kg                                 |
| Load capacity at 4 km/h     | 150 kg                                 |
| Load capacity Static        | 300 kg                                 |
| Temperature range (Minimum) | -20 °C                                 |
| Temperature range (Maximum) | 80 °C                                  |
| Overall height              | 150 mm                                 |
| Overall width               | 71 mm                                  |
| Overall weight              | 0.945 kg                               |
| Certification               | Tested and monitored by TÜV Süd        |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Polyamide                         |
| Tread material        | Polyurethane, injected            |
| Bearing               | Precision ball bearing, stainless |
| Threadguards          | With threadguard                  |
| Diameter              | 125 mm                            |
| Tread width           | 15 mm                             |
| Hardness of tread (A) | 92 Shore A                        |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Offset              | 40 mm                  |
| Swivel radius       | 102.5 mm               |
| Swivel interference | 205 mm                 |
| Stainless           | ✓                      |

## FITTING

|               |                                                                                    |
|---------------|------------------------------------------------------------------------------------|
| Fitting type  | Stem with cam hole for profile bars, short version                                 |
| Bolt diameter | 32 mm                                                                              |
| Bolt length   | 50 mm                                                                              |
| Hint          | Washable beds must be sealed in the fitting area by the hospital bed manufacturer. |



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award

# LINEA CLINIC

5946UAC125R36-32S30OH150 4XM6

EAN 4031582360028



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

