


NOVATECH

RK.ETP075X50-Ø47X12

EAN 4031582369496



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Nedefinisani
materijal omotaca	polipropilen, mekan
Prečnik	75 mm
Širina omotac	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Prečnik kuglicni lezaj	47 mm
Širina kuglicni lezaj	12 mm

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Nosivost na 3 km/h	500 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,549 kg

TEHNIČKI CRTEŽI

