

FOOTMASTER

FOOT MASTER GATD-100-ASF-HUD

EAN 4031582495249



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	310 kg
Električni provod	no
nerdjajuci	no
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	150 mm
Ukupna širina	131 mm
Ukupna težina	7.01 kg

KUCISTE

ofset	30 mm
okretni radijus	91 mm
Otpor okretanju	182 mm
Prečnik kupole	104 mm

TOCAK

Nošenje	Nemašinsko glavcina
Prečnik	100 mm
Širina omotac	30 mm
Širina tela	30 mm

PRILAGOĐAVANJE

Dužina ploče	112 mm
Širina ploče	112 mm
Dužina otvora ploče (maksimalna)	92 mm
Širina otvora ploče (maksimalna)	92 mm
Prečnik otvora ploče	9 mm

FOOTMASTER

FOOT MASTER GATD-100-ASF-HUD

EAN 4031582495249

Broj porudžbine 00800113
Product Drawings



BETTER MOBILITY. BETTER LIFE.

