

PRODUCT INFORMATION

NOVATECH

RK.ETP078x78-Ø47x16

EAN 4031582330069



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	78 mm
Tread width	78 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Ball bearing diameter	47 mm
Ball bearing width	16 mm

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	700 kg
Load capacity at 6 km/h	840 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.67 kg

