

STYLEA

5925UJI075B10-11X20

EAN 4031582456219



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	81 mm
Overall width	53 mm
Overall weight	0.19 kg

WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	62 mm
Swivel interference	124 mm
Dome diameter	22 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm