

STYLEA

5920XGI065L51-11 DOM23X43,6

EAN 4031582344868



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	✓
Load capacity Static	220.46 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.6 in
Overall width	1.81 in

WHEEL

Body material	Polyamide, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.28 in

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.09 in
Swivel interference	4.17 in
Dome diameter	0.91 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.43 in

PRODUCT INFORMATION

STYLEA

5920XGI065L51-11 DOM23X43,6

EAN 4031582344868



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

