

# STORA

2370DIK100P30-11

EAN 4031582300307



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	129 mm
Overall weight	0.795 kg

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Offset	35 mm
Swivel radius	85 mm
Swivel interference	170 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# STORA

2370DIK100P30-11

EAN 4031582300307



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

