

# MONO

A025PJI050L51-10 RAL7035

EAN 4031582359886



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	72 mm
Overall weight	0.78 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	18 mm
Hardness of tread (A)	85 Shore A

## HOUSING

Material fork	Polypropylene
Fork shape	Closed
Swivel bearing	Stem, swiveling
Colour	Light grey (RAL7035)
Offset	25 mm
Swivel radius	71.8 mm
Swivel interference	143.6 mm

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

# MONO

A025PJI050L51-10 RAL7035

EAN 4031582359886



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

