

AGILA

2477DIK150R05-28 M8/19

EAN 4031582301946
Order number 00030775



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	188 mm
Overall width	60 mm
Overall weight	1.744 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	36 mm
Swivel radius	131 mm
Swivel interference	262 mm
Dome diameter	60 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm
Bolt thread position	19 mm
Bolt mounting holes quantity	2

AGILA

2477DIK150R05-28 M8/19

EAN 4031582301946
Order number 00030775



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

