

PURETECH

PVR 125X37-Ø12 HL44

EAN 4031582321265
Broj porudžbine 00030955

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Puretech

Tip Tocak

Standard EN12532 - transportna oprema

Nosivost na 4 km/h 100 kg

Statički Nosivost 200 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

Ukupna težina 0,467 kg

TOCAK

Materijal za telo polipropilen

materijal omotaca Cvrsta guma crna

Nošenje kotrljajući lezaj

Boja Tocak Grafitna crna (RAL9011)

stitnici omotaca Bez stražara

Prečnik 125 mm

Širina omotac 37 mm

dimenzija rupa osovina 12 mm

dužina glavcine 44 mm

Širina tela 37 mm

Teškoća gazećeg omotac (A) 80 Šešelj A

PURETECH

PVR 125X37-Ø12 HL44

EAN 4031582321265
Broj porudžbine 00030955



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

