

ELASTECH

UFP100X34-Ø8

EAN 4031582338690
Broj porudžbine 00031810

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	34 mm
dimenzija rupa osovina	8,3 mm
dužina glavcine	45 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●●

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,294 kg

ELASTECH

UFP100X34-Ø8

EAN 4031582338690
Broj porudžbine 00031810



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

