PRODUCT INFORMATION

AVIANA

5976UAE075P54 light 7001 bk+washer

EAN 4031582396638

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Aviana
Type	Swivel castor with central, total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	102 mm
Overall width	69 mm
Overall weight	0.37 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Two ball races
Housing Color	Silver grey (RAL7001)
Offset	28 mm
Swivel radius	68.5 mm
Swivel interference	137 mm
Dome diameter	54 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Cone ball bearing, stainless
Wheel Color	Slate grey (RAL7015)
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate with brake elements
Plate length	70 mm
Plate width	55 mm
Plate hole length (Minimum)	51 mm
Plate hole length (Maximum)	41 mm
Plate hole width (Minimum)	51 mm
Plate hole width (Maximum)	57 mm
Plate hole diameter	5.5 mm

Red Dot Design Award

German Design Award

© Copyright 2026 TENTE International GmbH


AVIANA


5976UAE075P54 light 7001 bk+washer


EAN 4031582396638


TENTE
BETTER MOBILITY. BETTER LIFE.

Product Drawings









Red Dot Design Award

German Design Award

© Copyright 2026 TENTE International GmbH