PRODUCT INFORMATION

ELASTECH

SEP 200x50-Ø20 HL60 plus

EAN 4031582346671

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Sheet steel, heavy
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1102.31 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	7.67 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

SEP 200x50-Ø20 HL60 plus

EAN 4031582346671

Order number 00834217

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

SEP 200x50-Ø20 HL60 plus

EAN 4031582346671

Order number 09834217



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH