

# STYLEA

5925UJI065S70-10X15

EAN 4031582456059



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Stylea                         |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Temperature range (Minimum) | -10 °C                         |
| Temperature range (Maximum) | 40 °C                          |
| Overall height              | 74 mm                          |
| Overall width               | 42 mm                          |
| Overall weight              | 0.19 kg                        |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 65 mm                          |
| Tread width           | 7 mm                           |
| Hardness of tread (D) | 75 Shore D                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Swivel radius       | 62 mm              |
| Swivel interference | 124 mm             |
| Dome diameter       | 23 mm              |
| Thread diameter     | 10 mm              |

## FITTING

|              |                                      |
|--------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem length  | 15 mm                                |