

## DIZAJN POKLOPCA

2074PIP125R26-28S45

EAN 4031582360868



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Dizajn poklopca
Tip	Okreni Tocak sa centralnom, totalnom ili usmerena kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	163 mm

## TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	32 mm
Teškoća gazaćeg omotac (A)	75 Šor A

## KUCISTE

Materijal	Čelični list, srednji
oblik viljuska	Zatvoreno
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	103,5 mm
Otpor okretanju	207 mm

## PRILAGOĐAVANJE

Tip uklapanja	stablo sa bregasta rupa za trake profila
Prečnik sraf	28 mm
Dužina sraf	96 mm



Red Dot Dizajn Award

# DIZAJN POKLOPCA

2074PIP125R26-28S45

EAN 4031582360868



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---



Red Dot Dizajn  
Award