

# COMPACTA

1298UOI014P80-26

EAN 4031582300024  
Order number 00021119



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Compacta                    |
| Housing type                | Fixed castor                |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 15 kg                       |
| Load capacity Static        | 30 kg                       |
| Temperature range (Minimum) | -20 °C                      |
| Temperature range (Maximum) | 60 °C                       |
| Overall height              | 13.5 mm                     |
| Overall width               | 19 mm                       |
| Overall weight              | 0.008 kg                    |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Wheel color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 14 mm                          |
| Tread width           | 14 mm                          |
| Body width            | 14 mm                          |
| Hardness of tread (D) | 65 Shore D                     |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material fork | Steel sheet, light |
| Fork shape    | Straight           |
| Colour        | Blue passivated    |
| Dome diameter | 19 mm              |

## FITTING

|                             |             |
|-----------------------------|-------------|
| Fitting type                | Round plate |
| Plate hole length (Maximum) | 20 mm       |
| Plate hole width (Maximum)  | 20 mm       |
| Plate hole diameter         | 2.5 mm      |

# COMPACTA

1298UOI014P80-26

EAN 4031582300024  
Order number 00021119



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

