

ZETA

4680PVR250P63

EAN 4031582327663



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	295 kg
Load capacity at 6 km/h	250 kg
Load capacity Static	590 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	290 mm
Overall weight	4.834 kg

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Hardness of tread (A)	67 Shore A

HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel radius	180 mm
Swivel interference	360 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA

4680PVR250P63

EAN 4031582327663



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

