PRODUCT INFORMATION

# MONO

## 5020PJH080S70-10X15 TFR

EAN 4031582385755



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●●○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Mono |
| Type | Swivel caster |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 154.32 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 308.65 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 4.33 in |
| Overall weight | 0.4 lb |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Closed |
| Swivel bearing | Stem, swiveling |
| Offset | 1.34 in |
| Swivel radius | 2.91 in |
| Swivel interference | 5.83 in |
| Thread diameter | 0 in |

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Threadguards | With threadguard |
| Diameter | 3.15 in |
| Tread width | 0.94 in |
| Hardness of tread (A) | 87 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem diameter | 0.39 in |
| Stem length | 0.59 in |

© Copyright 2026 TENTE International GmbH


# MONO

## 5020PJH080S70-10X15 TFR

EAN 4031582385755

BETTER MOBILITY. BETTER LIFE.

### Product Drawings



© Copyright 2026 TENTE International GmbH